


## Here are the connections for the P48 High Z buffer for Piezo hydrophones

The outside silver plating goes to “SGNL”.  
The inside silver plating is connected to “GND”.

With P48 applied:  
VCC\_1 = 11.5-12VDC  
VCC\_2 = 11.3-11.8VDC  
XLR\_2 and XLR\_3 = 20-22VC

This circuit is suitable for any piezo pickup or contact microphone. For contact microphones, ensure you use adequate shielding.



**NOTE: Pay attention to XLR Pin Numbers. They are printed on most connectors. Look Closely**